

Breathing apparatus Interspiro Spiroguide II

100028

A close cooperation with firefighters and experts in the field of ergonomics has been a defining feature when developing the Spiroguide II harness. The ergonomic design of all the components and the many integrated smart features make the harness highly versatile. Each component is carefully selected to ensure that the harness is robust enough to handle the extreme environment for which it is intended.

The harness can easily be adjusted for different body sizes in four different size settings ("S", "M", "L", "XL"). The selected size is clearly visible from both the front and the back. Thanks to the practical design the size adjustment can be made with the cylinder mounted and without removing the apparatus from the fire truck.

The Spiroguide II has an ergonomic and easy-to-read display with powerful backlight and two big buttons. It is designed and built to work, whatever the conditions.

The digital display can be configured to show one or more of these screens:

- Cylinder pressure in bar
- Cylinder pressure symbol
- Remaining air time based on actual breathing rate
- Absorbed temperature

An automatic motion and panic alarm with motion sensor is fully integrated with the Spiroguide II. It can be activated either with a tally key or automatically when the unit is pressurized. The manual override button is located on the display unit and is easy to find while being hard to press by mistake.

The distinct turn-back signal is an additional warning level for added safety. It can be configured to activate at a specific level above the low air warning or configured to automatically set the level depending on start pressure.

The unit is recording cylinder pressure, unit status, warnings and temperatures to a log file with date and time for every event.

As an additional safety feature, the Spiroguide II conducts an automatic startup test checking cylinder pressure and electronic functions. This test requires no user interaction until the test is completed and the result acknowledged by the user.

Back at the station, the full start-up test is performed to check vital SCBA functions, including leakage, air flow and motion alarm functions. The user friendly step-by-step instructions on the display guide the user during the test. A service mode can be access directly on the display unit showing relevant service data.



"Vatropromet" company is an authorized Interspiro respirator service and we provide complete support for the maintenance and servicing of respirators.

Technical specifications

Characteristics:

- Hip belt and shoulder straps move independently for maximum mobility
- Ergonomically shaped shoulder straps and hip belt
- Large rescue handle - easy to grab to drag out fire fighter in an emergency
- Open back plate for good ventilation and low weight
- Easy to handle and adjustable cylinder strap
- Interchangeable hose holders
- Flexible mounting system for accessories
- Small and light warning whistle
- Large size text with powerful backlight makes the display easy to read

Approval: CE 89/686/EEC	Approval (2) EMC 89/336/EEC
Standard: EN 137, tip 2	Material: Heat resistant polymer backplate
Material (2): Kevlar webbing	Connection: Cylinder - EN 144 / QC
Air flow: 1350 l/min.	Warning: electronic 105 dBA
Weight: 4.3 kg (excl. mask & breathing valve)	Battery type: 3 xAAA

The Spiroguide II SCBA can be combined with different face mask and breathing valve models. The SCBA variants exclude face mask, breathing valve and cylinder.

Variants are available having a quick coupling with integrated flow restrictor between regulator and cylinder.

Variants are available without extra connections ("Basic configuration") or with extra connections for breathing hose and/or extra air connection for airline supply.

All variants include mechanical pressure gauge. Variants are available including or excluding a mechanical warning whistle.

The optional wireless Heads-up display, see "Accessories" below, gives a handsfree indication of cylinder pressure and with the "buddy reading" function it is visible for other team members.

The Spiroguide II SCBA can be used in single cylinder or twin cylinder configuration. An optional holder to park the breathing valve is available for some breathing valve models.

